




AVT 1572



ASSEMBLY DIFFICULTY



There is no need to convince any practitioner how useful a device a power supply is in the laboratory, while a beginner will quickly learn that nothing can be done without it. The devices being run very often require a symmetrical power supply, and the single-voltage power supplies can't always be connected in series to get the voltage you need. Thus, the presented power supply is another device that expands the capabilities of our workshop.

Characteristics

- positive and negative output voltages
- adjustable output voltages $1,2 \dots 25 \text{ V DC}$
- maximum continuous output current: $2 \times 1,5 \text{ A}$
- output voltage indicator lights – LEDs
- short circuit and thermal protection
- recommended transformer: $2 \times 17 \dots 19 \text{ V AC}$
- board dimensions: $45 \times 81 \text{ mm}$

Circuit description

The schematic diagram is shown in Fig. 1. The reference voltage is set using the PR1 and PR2 potentiometers. LM317 is a positive voltage regulator while LM337 is a negative voltage one. LM circuits need only a few external components and have built-in thermal protection as well as current limiting when the output is shorted to ground. The output voltage range for a $2 \times 17 \dots 19 \text{ V AC}$ supply is $\pm 1,25 \text{ V}$ to $\pm 25 \text{ V}$. The LM317 and LM337 circuits have built-in short-circuit and

thermal protection.

When selecting a transformer, pay attention to the voltage rating of the C1 and C2 capacitors. The transformer should be selected so that its secondary voltage after rectification through the M1 bridge is no greater than the rated voltage of the capacitors.

Assembly and start-up

The assembly diagram is shown in Fig. 2. The assembly must start by soldering the "Z" jumper and the last components to be assembled must be the C1 and C2 capacitors, just after screwing the circuits to the heatsink. Insulate the US1 and US2

circuits from the heat sink with a mica or silicone spacer. The assembly is typical, and the circuit, assembled from working components, does not require any adjustment. Once connected to the transformer it immediately works properly.




Fig. 1 Schematic diagram of the power supply




Fig. 2 Layout of the components on the circuit board

List of elements

Resistors:

R1, R3:2,2k Ω

R2, R4:220 Ω

PR1, PR2:linear 5 k Ω

Capacitors:

C1, C2:2200 uF / 35 V

C3, C4, C7, C8:100 nF

C5, C6, C9, C10:10 uF / 63 V

Semiconductors:

US1:LM317

US2:LM337

D1-D4:1N4007

LED1, LED2:red 3 mm


M1:bridge rectifier

Other:

X1, X2:DG301-5.0/3

TO220 silicon washers $\times$ 2 Spacers $\times$ 2

Screws $\times$ 3 Radiator



EDUCATIONAL
ELECTRONIC
KITS

AVT SPV Sp. z o.o.

Leszczynowa 11 Street,
03-197 Warsaw, Poland
kity@avt.pl



CE



This symbol means do not dispose of your product with your other household waste. Instead, you should protect human health and the environment by handing over your waste equipment to a designated collection point for the recycling of waste electrical and electronic equipment.

AVT SPV reserves the right to make changes without prior notice. Assembly and connection of the device not in accordance with the indications within the instructions, arbitrary change of components and any structural modifications may cause damage to the device and expose users to harm. In such a case, the manufacturer and its authorized representatives shall not be liable for any damages arising directly or indirectly from the use or malfunction of the product. DIY kits are intended for educational and demonstration purposes only. They are not intended for use in commercial applications. If they are used in such applications, the buyer assumes all responsibility for ensuring compliance with all regulations.