



Philips EasySense Outboard-Mount for High Bay Quick Installation Guide

Philips EasySense SNH210 MC is a DLC-qualified network lighting control (NLC) solution for industrial high bay applications that connects with the Philips Advance Xitanium SR LED Drivers and works with the updated Philips field app MC.



EasySense quick guide



Occupancy Sensing Detection Pattern

The plots below show the top and side view of the occupancy coverage based on NEMA test, an industry standard. In the side view, it is visible that coverage ration of height:diameter is 1:1. For example if the mounting height is 12m, the diameter coverage is also 12m.

Disclaimer:

1. In these plots, the white areas are blind spots and the detection is based on subject's motion.
An idle subject may not continue to trigger occupancy detection once the hold time collapses.
2. As PIR based sensing works on temperature difference between the subject and the ground level, the occupancy detection could vary due to clothing and size of humans.

Special Note: Ensure heat radiating devices are outside of the monitoring cone.
Avoid drafts (e.g. from ventilators or heating systems).




Daylight Sensor

The light sensor measures the total amount of light with an opening angle of 10 degrees whereas the PIR has an angle of 30 degrees, all calculated from normal. The following aspects should be observed during installation:

- Minimum distance from the window: see graph below
- Prevent light reflections from outside entering the sensor (for example sunlight reflection on a car bonnet) as this will lead to incorrect light regulation.

As a guideline the formula $0.174 \times H$ can be used to calculate the minimum distance between the window and sensor whereby H is the height from the bottom of the window to the ceiling.

Photosensor spatial response



Minimum distance from window vs. mounting height



Note: Restrictions only for daylight regulation. No restrictions for skylights.



EasySense quick guide

Configuration via Mobile App

Note: EasySense parameters can be configured via Philips field app MC which is available for both Apple and Android smart phones.

You must first download the Philips field app MC from either the Google Play store or App store, then register to receive a username and password. Refer to www.philips.com/easysense for details, including applicable phones and user manuals.

FCC and IC Statement This device complies with part 15 of the FCC rules for the United States and Industry Canada (IC) license-exempt RSS standard(s). Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. Any changes or modifications not expressly approved by Philips could void the user's authority to operate this equipment. This product is intended for commercial use only.

This equipment should be installed and operated with a minimum distance of 20cm between the radiator and your body.

Déclaration De Conformité À La Fcc/Ic Ce dispositif est conforme à la partie 15 des règles de la Federal Communications Commission (FCC) des États-Unis et d'Industrie Canada (IC) exempts de licence RSS norme(s). Son fonctionnement est assujéti aux deux conditions suivantes: (1) Ce dispositif ne doit pas provoquer de brouillage préjudiciable, et (2) il doit accepter tout brouillage reçu, y compris le brouillage pouvant entraîner un mauvais fonctionnement. Tous les changements ou modifications non expressément approuvés par Philips, sont susceptibles d'annuler le droit de l'utilisateur à se servir de cet équipement. Ce produit est exclusivement destiné à un usage commercial.

Cet équipement doit être installé et utilisé avec une distance minimale de 20 cm entre le radiateur et votre corps.

Sensor part number

Commercial Product Name	Order Code
EasySense Outboard-Mount for High Bay	SNH210 MC

Compatible LED drivers

The EasySense SNH210 MC is compatible with Xitanium SR drivers. To find the SR driver that fits your needs and for product specifications, please visit www.philips.com/xitanium/na

© 2021 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

PLT-17265QG 04/21 philips.com/lighting page 4 of 4



Signify North America Corporation
200 Franklin Square Drive,
Somerset, NJ 08873
Telephone 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.

